


RACOR DE IMPLANTACIÓN: Racor de entrada, Recto rosca BSP cilíndrica



Dimensiones

Código	ØD (mm)	C	F (mm)	F1 (mm)	Hmaxi (mm)	H1 (mm)	H2 (mm)	 (kg)
0114 04 13	4	G1/4	17	10	30	20.5	13.5	0.03
0114 05 10	5	G1/8	14	12	28	17	9.5	0.02
0114 06 10	6	G1/8	14	13	28	17	9.5	0.02
0114 06 13	6	G1/4	17	13	32	21	13.5	0.03
0114 06 17	6	G3/8	22	13	32	21.5	14	0.05
0114 08 10	8	G1/8	14	14	29	16.5	9.5	0.03
0114 08 13	8	G1/4	17	14	33	20.5	13.5	0.04
0114 08 17	8	G3/8	22	14	34	21	14	0.05
0114 10 13	10	G1/4	17	19	37	21.5	13.5	0.05
0114 10 17	10	G3/8	22	19	37	22	14	0.07
0114 10 21	10	G1/2	27	19	42	26.5	18.5	0.1
0114 12 13	12	G1/4	19	22	36	20.5	13.5	0.07
0114 12 17	12	G3/8	22	22	37	22	14	0.08
0114 12 21	12	G1/2	27	22	42	26.5	18.5	0.11
0114 14 17	14	G3/8	22	24	38	21	14	0.08
0114 14 21	14	G1/2	27	24	43	25.5	18.5	0.11
0114 15 17	15	G3/8	22	24	38	21	14	0.08
0114 15 21	15	G1/2	27	24	43	25.5	18.5	0.11
0114 16 17	16	G3/8	24	27	38	20.5	14	0.11
0114 16 21	16	G1/2	27	27	44	26	18.5	0.13
0114 18 21	18	G1/2	27	30	45	26	18.5	0.14

RACORES UNIVERSALES DE LATÓN

0114 18 27	18	G3/4	32	30	46	27	19.5	0.17
0114 20 21	20	G1/2	30	32	44.5	24	18.5	0.17
0114 22 27	22	G3/4	32	36	48	26.5	19.5	0.2

Especificaciones

La presión máxima de un circuito depende de la calidad y el diámetro d el tubo, y de la temperatura.

	°C (Celsius)	F (Fahrenheit)	K (Kelvin)
temperatura de utilización	de -40 a 100	de -40 a 212	de 233 a 373

cuerpo latón